


Varistar CP Cabinet Frame, 42 U, 2000H, 800W, 800D

Data Solutions

KATALOGNUMMER

20630-106



Varistar CP welded frame is available for static load requirements and can be integrated with 19", ETSI or mounting plate. Additionally, castors can be added to the frame if needed.

However, if you require castors for your application, you might want to consider a mobile frame that already includes castors.

DESIGN

Welded, finish powder-coated, black gray, RAL 7021

St, 1.5 mm, zinc-plated, with central GND/grounding point

Static load-carrying capacity max. 1600 kg

Please order adjustable feet separately

PRODUKTATTRIBUT

Rackhöjd: 42U

Höjd: 2000mm

Bredd: 800mm

Djup: 800mm

Antal i förpackningen: 1

Färg: Svartgrå

Färgkod: RAL 7021

Rammaterial: Stål

Material: Stål

Produktfamilj: Varistar CP

Produkttyp: Skåp/rackram

Statisk belastning: 1600kg

Typ: Standard

Fungerar med: Varistar CP

YTTERLIGARE PRODUKTINFORMATION

Castor can be added to the frame. If you will need a castor for your application, you can order a mobile frame which include castors.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE