

Single Temperature and Humidity Sensor

Data Solutions

KATALOGNUMMER

EA9103



Single Temperature and Humidity Probe Sensor for nVent SCHROFF RackPower PDU's.

DESIGN

Single Temperature and Humidity Sensor

With 2 Meter cable and integrated magnet for easy mounting

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Temperature Measuring Range 0 to 65 °C

Temperature Measuring Accuracy +/- 2 %

Humidity Measuring Range 10-90% RH, Non-Condensing

Humidity Measuring Accuracy +/- 5 %

PRODUKTATTRIBUT

Produkttyp: Givare

Fungerar med: Rackeffekt

Höjd: 270mm

Antal i förpackningen: 1

Kontakttyp: RJ45

Produktfamilj: Enlogic

Löstagbar ingångskabel: Nej

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE