

Telescopic Slides C-Profile for Cabinet

Data Solutions



Telescopic slides with guiding profile for fitting in cabinets with 25 kg load capacity.

CERTIFIERINGAR



DESIGN

For mounting 84 HP wide subracks in the 19" plane

Loading capacity: 25 kg per pair

The guiding profile (1) is matched to the fixing dimension in the cabinet (it is bolted to the 19" profile of the cabinet); the adaptor Rail (3) is matched to the depth and fixing dimension on the subrack (it is inserted into the guiding profile like a telescopic slide)

SPECIFIKATIONER

Material:	Aluminium
Yta:	Anodiserad
Typ:	C-profil
Produkttyp:	Teleskopskena

Table 1/1

Katalognummer	Djup	Antal i förpackningen
---------------	------	-----------------------

24562-473	1200mm	2
24562-446	250mm	2
24562-449	600mm	2
24562-451	800mm	2
24562-452	900mm	2
24562-460	500mm	2
24562-461	600mm	2
24562-464	600mm	2
24562-466	800mm	2
24562-467	900mm	2
24562-468	1000mm	2
24562-472	1100mm	2
24562-474	800mm	2

YTTERLIGARE PRODUKTINFORMATION

No protection against extraction, no stop at full extension.

The reinforcement Rail and the C-Rails have been tested in accordance with the Russian atomic energy authority GAN standards.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE