

Varistar Colocation Cabinet, RAL 7035

Data Solutions



Colocation cabinets with 2, 3 or 4 divider units in RAL 7035 to accommodate servers while separating access and cabling of the compartments.

CERTIFIERINGAR



DESIGN

Colocation cabinets with compartments to accommodate e.g. servers

Flexible cabling, possible from above, below, left or right (data and power cables can be run separately)

Multi-point door locking

Perforated doors

Protection class IP 20

Color RAL 7035

SPECIFIKATIONER

Produkttyp: Rack

Rammaterial: Stål

Table 1/3

Katalognummer	Rackhöjd	Höjd	Pläteringsmaterial	Ramfärg	Bredd	Ramfärgkod
---------------	----------	------	--------------------	---------	-------	------------

11130-202	40U	2000mm	Stål	Ljusgrå	600mm	RAL 7021
11130-203	39U	2000mm	Stål	Ljusgrå	600mm	RAL 7021
11130-204	40U	2000mm	Stål	Ljusgrå	600mm	RAL 7021
11130-205	40U	2000mm	Stål	Ljusgrå	800mm	RAL 7021
11130-206	39U	2000mm	Stål	Ljusgrå	800mm	RAL 7035
11130-207	40U	2000mm	Stål	Ljusgrå	800mm	RAL 7021
11130-208	44U	2200mm	Stål	Ljusgrå	600mm	RAL 7021
11130-209	45U	2200mm	Stål	Ljusgrå	600mm	RAL 7021
11130-210	44U	2200mm	Stål	Ljusgrå	600mm	RAL 7021
11130-211	44U	2200mm	Stål	Ljusgrå	800mm	RAL 7021
11130-212	45U	2200mm	Stål	Svartgrå	800mm	RAL 7021
11130-213	44U	2200mm	Stål	Ljusgrå	800mm	RAL 7021
11130-214	40U	2000mm	Stål	Ljusgrå	600mm	RAL 7021
11130-215	39U	2000mm	Stål	Ljusgrå	600mm	RAL 7021
11130-216	40U	2000mm	Stål	Ljusgrå	600mm	RAL 7021
11130-217	40U	2000mm	Stål	Ljusgrå	800mm	RAL 7021
11130-218	39U	2000mm	Stål	Svartgrå	800mm	RAL 7021
11130-219	40U	2000mm	Stål	Ljusgrå	800mm	RAL 7021
11130-220	44U	2200mm	Stål	Ljusgrå	600mm	RAL 7021

11130-221	45U	2200mm	Stål	Ljusgrå	600mm	RAL 7021
11130-222	44U	2200mm	Stål	Ljusgrå	600mm	RAL 7021
11130-223	44U	2200mm	Stål	Ljusgrå	800mm	RAL 7021
11130-224	45U	2200mm	Stål	Ljusgrå	800mm	RAL 7021
11130-225	44U	2200mm	Stål	Ljusgrå	800mm	RAL 7021
11130-257	45U	2450mm	Stål	Ljusgrå	600mm	RAL 7021
11130-258	48U	2450mm	Stål	Ljusgrå	600mm	RAL 7021
11130-259	48U	2450mm	Stål	Ljusgrå	600mm	RAL 7021
11130-260	45U	2450mm	Stål	Ljusgrå	800mm	RAL 7021
11130-261	48U	2450mm	Stål	Ljusgrå	800mm	RAL 7021
11130-262	48U	2450mm	Stål	Ljusgrå	800mm	RAL 7021
11130-269	45U	2450mm	Stål	Ljusgrå	600mm	RAL 7021
11130-270	48U	2450mm	Stål	Ljusgrå	600mm	RAL 7021
11130-271	48U	2450mm	Stål	Ljusgrå	600mm	RAL 7021
11130-272	45U	2450mm	Stål	Ljusgrå	800mm	RAL 7021
11130-273	48U	2450mm	Stål	Ljusgrå	800mm	RAL 7021
11130-274	48U	2450mm	Stål	Ljusgrå	800mm	RAL 7021

Table 2/3

Katalognummer	Pläteringsfärg	Plätering, färgkod	Djup	Antal i förpackningen	Antal fack	Yta
---------------	----------------	--------------------	------	-----------------------	------------	-----

11130-202	Ljusgrå	RAL 7035	1000mm	1	2	Pulverlackerad
11130-203	Ljusgrå	RAL 7035	1000mm	1	3	Pulverlackerad
11130-204	Ljusgrå	RAL 7035	1000mm	1	4	Pulverlackerad
11130-205	Ljusgrå	RAL 7035	1000mm	1	2	Pulverlackerad
11130-206	Ljusgrå	RAL 7035	1000mm	1	3	Pulverlackerad
11130-207	Ljusgrå	RAL 7035	1000mm	1	4	Pulverlackerad
11130-208	Ljusgrå	RAL 7035	1000mm	1	2	Pulverlackerad
11130-209	Ljusgrå	RAL 7035	1000mm	1	3	Pulverlackerad
11130-210	Ljusgrå	RAL 7035	1000mm	1	4	Pulverlackerad
11130-211	Ljusgrå	RAL 7035	1000mm	1	2	Pulverlackerad
11130-212	Ljusgrå	RAL 7035	1000mm	1	3	Pulverlackerad
11130-213	Ljusgrå	RAL 7035	1000mm	1	4	Pulverlackerad
11130-214	Ljusgrå	RAL 7035	1200mm	1	2	Pulverlackerad
11130-215	Ljusgrå	RAL 7035	1200mm	1	3	Pulverlackerad
11130-216	Ljusgrå	RAL 7035	1200mm	1	4	Pulverlackerad
11130-217	Ljusgrå	RAL 7035	1200mm	1	2	Pulverlackerad
11130-218	Ljusgrå	RAL 7035	1200mm	1	3	Pulverlackerad
11130-219	Ljusgrå	RAL 7035	1200mm	1	4	Pulverlackerad
11130-220	Ljusgrå	RAL 7035	1200mm	1	2	Pulverlackerad

11130-221	Ljusgrå	RAL 7035	1200mm	1	3	Pulverlackerad
11130-222	Ljusgrå	RAL 7035	1200mm	1	4	Pulverlackerad
11130-223	Ljusgrå	RAL 7035	1200mm	1	2	Pulverlackerad
11130-224	Ljusgrå	RAL 7035	1200mm	1	3	Pulverlackerad
11130-225	Ljusgrå	RAL 7035	1200mm	1	4	Pulverlackerad
11130-257	Ljusgrå	RAL 7035	1000mm	1	2	Pulverlackerad
11130-258	Ljusgrå	RAL 7035	1000mm	1	3	Pulverlackerad
11130-259	Ljusgrå	RAL 7035	1000mm	1	4	Pulverlackerad
11130-260	Ljusgrå	RAL 7035	1000mm	1	2	Pulverlackerad
11130-261	Ljusgrå	RAL 7035	1000mm	1	3	Pulverlackerad
11130-262	Ljusgrå	RAL 7035	1000mm	1	4	Pulverlackerad
11130-269	Ljusgrå	RAL 7035	1200mm	1	2	Pulverlackerad
11130-270	Ljusgrå	RAL 7035	1200mm	1	3	Pulverlackerad
11130-271	Ljusgrå	RAL 7035	1200mm	1	4	Pulverlackerad
11130-272	Ljusgrå	RAL 7035	1200mm	1	2	Pulverlackerad
11130-273	Ljusgrå	RAL 7035	1200mm	1	3	Pulverlackerad
11130-274	Ljusgrå	RAL 7035	1200mm	1	4	Pulverlackerad

Table 3/3

Katalognummer	Material	Statisk belastning
11130-202	Stål	800kg

Katalognummer	Material	Statisk belastning
11130-203	Stål	800kg
11130-204	Stål	800kg
11130-205	Stål	800kg
11130-206	Stål	800kg
11130-207	Stål	800kg
11130-208	Stål	800kg
11130-209	Stål	800kg
11130-210	Stål	800kg
11130-211	Stål	800kg
11130-212	Stål	800kg
11130-213	Stål	800kg
11130-214	Stål	800kg
11130-215	Stål	800kg
11130-216	Stål	800kg
11130-217	Stål	800kg
11130-218	Stål	800kg
11130-219	Stål	800kg
11130-220	Stål	800kg

Katalognummer	Material	Statisk belastning
11130-221	Stål	800kg
11130-222	Stål	800kg
11130-223	Stål	800kg
11130-224	Stål	800kg
11130-225	Stål	800kg
11130-257	Stål	800kg
11130-258	Stål	800kg
11130-259	Stål	800kg
11130-260	Stål	800kg
11130-261	Stål	800kg
11130-262	Stål	800kg
11130-269	Stål	800kg
11130-270	Stål	800kg
11130-271	Stål	800kg
11130-272	Stål	800kg
11130-273	Stål	800kg
11130-274	Stål	800kg

YTTERLIGARE PRODUKTINFORMATION

Side panel must be ordered separately. For suitable cable panel see Accessories.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE