

EB-12 jordning och neutral samlingskena



nVent ERIFLEX Connecting, Earthing and Neutral Busbars are used to connect several earthing conductors within a panel and can be used in a variety of different applications including switchgear and control equipment, electrical equipment, for wind and solar power generation and in data centers.

CERTIFIERINGAR



DESIGN

Uppfyller RoHS

Use to connect several earthing conductors

Chamfered holes allow for easy connections

Rigid bar


SPECIFIKATIONER

Material: Mässing

Katalognummer	EB12	EB12BLK200
Artikelnummer	568610	568611
Antal anslutningar	12	12
Ledarstorlek, IEC	(2) 16 - 35 mm ² flertrådig (10) 4 - 16 mm ² Stranded	(2) 16 - 35 mm ² flertrådig (10) 4 - 16 mm ² Stranded
Ledningshylsa, storlek, IEC	(2) 10-35 mm ² (10) 2.5 - 16 mm ²	(2) 10-35 mm ² (10) 2.5 - 16 mm ²

Katalognummer	EB12	EB12BLK200
Ledarstorlek, UL	(2) #6 Solid (10) #8 - #6 Solid (2) #6 Stranded (10) #8 - #6 Stranded	(2) #6 Solid (10) #8 - #6 Solid (2) #6 Stranded (10) #8 - #6 Stranded
Max. strömstyrka	250A	250A
Djup (D)	6mm	6mm
Höjd (H)	13 mm	13 mm
Bredd (W)	120 mm	120 mm
A.	105 mm	105 mm
B.	9 mm	9 mm
Enhetens vikt	0.07 kg	0.07 kg
Överensstämmer med.	IEC® 61439,1	IEC® 61439,1

DIAGRAMS



VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE