

CS480 vridbar bas extern



CS480 Swivel Base External allows the entire suspension system to rotate at the point of attachment on a horizontal surface. Arm can be rotated or turned 340 degrees. Base mounting hardware is exposed. Maintenance-free bearings.

BRANSCHSTANDARDER

IEC 60529, IP66

DESIGN

Base can rotate 340 degrees with rotation stop

Torque preset at factory

Gasket is included

Surface mounting fasteners are not provided

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

SPECIFIKATIONER

Table 1/1

Katalognummer	Höjd	Bredd	Djup	Material	Slutför	Snabbleverans
CCSS48BBRE	110mm	149mm	149mm	Rostfritt stål 304	Borstad	Nej

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE