

CS480 väggkoppling



CS480 Wall Coupling mounts the enclosure directly to a wall or vertical surface, enabling 340-degree enclosure rotation. Cover to facilitate wiring. Maintenance-free bearings.

BRANSCHSTANDARDER

IEC 60529, IP66

DESIGN

Coupling can rotate 340 degrees with rotation stop

Torque preset at factory

Gasket and mounting hardware are included

Surface mounting fasteners are not provided

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

SPECIFIKATIONER

Table 1/1						
Katalognummer	Höjd	Bredd	Djup	Material	Yta	Snabbleverans
CCSS48WJC	177mm	129mm	150mm	Rostfritt stål 304	Borstad	Nej

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE