

Genomföringsböj på 90 grader, utvändig öppning på ovansidan, gångjärnsförsett skyddsinnlägg



Lay-in Hinged-Cover 90-Degree Elbow with Outside Top Opening are used for right-angle wireway installations. This elbow fitting allows a vertical drop to equipment below at a 90-degree corner while maintaining the top opening lay-in feature.

DESIGN

Lay-in Hinged-Cover 90-Degree Elbow with Outside Top Opening are used for right-angle wireway installations

This elbow fitting allows a vertical drop to equipment below at a 90-degree corner while maintaining the top opening lay-in feature

SPECIFIKATIONER

Färgkod: ANSI 61
Yta: Galvaniserad; Pulverlackerad
Färg: Grå
Material: Stålblåt

Table 1/1

Katalognummer	Typ	Höjd	Bredd	Tjocklek	Typ av tätningsplatta	Antal tätningsplattor
F88LE9AC	Vinkel	203mm	203mm	1.9mm	Flat	2
F66LE9AC	Vinkel	152mm	152mm	1.9mm	Flat	2
F44LE9AC	Vinkel	102mm	102mm	1.9mm	Flat	2

YTTERLIGARE PRODUKTINFORMATION

Each sealing plate also includes one gasket and one set of screws to join sections.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE