

Invändiga sidopaneler för strömdistribution, MSPS



The galvanised steel internal side panels, MSPS, segregate vertical sections and allow for mounting of busbar supports, MSHS, as well as other accessories. It is a flexible solution both for fix and plug in systems and allows for meeting form 4 segregation according to IEC 61439.

DESIGN

Beskrivning: Internal side panels to build up sections as from the enclosure frame. Frame hole pattern is needed in front, rear, top and bottom.

Material: 1.5 mm galvanized steel.

Leverans: 1 piece with mounting material.

The side panels segregate vertical sections, allowing customer's to mount main busbar supports (MSHS) and other accessories

A flexible solution for both fix and plug-in systems

The side panels allow customers to build up power distribution configurations to meet form 4 segregation according to IEC 61439

Hole patterns are required in the top, bottom, front and rear of the enclosure, in order to mount the internal side panels

SPECIFIKATIONER

Tjocklek: 1.5mm
Slutför: Galvaniserad
Material: Stål

Table 1/1

Katalognummer	E-nummer	Höjd	Bredd	Djup	Panelstorlek	Kapslingsmaterial
MSPS1803	2505143	1800mm	88.5mm	300mm	1800 x 337mm	Mjukt stål
MSPS1805	2504768	1800mm	88.5mm	500mm	1800 x 337mm	Mjukt stål
MSPS1806	2505144	1800mm	26mm	600mm	1800 x 507mm	Mjukt stål
MSPS1806F	2505041	1800mm	26mm	600mm	1800 x 507mm	Mjukt stål
MSPS1808		1800mm	26mm	800mm	1800 x 507mm	Mjukt stål
MSPS1808F		1800mm	26mm	800mm	1800 x 507mm	Mjukt stål
MSPS2003	2505145	2000mm	88.5mm	300mm	2000 x 337mm	Mjukt stål
MSPS2005	2504770	2000mm	88.5mm	500mm	2000 x 337mm	Mjukt stål
MSPS2006	2505146	2000mm	26mm	600mm	2000 x 507mm	Mjukt stål
MSPS2006F	2505042	2000mm	26mm	600mm	2000 x 507mm	Mjukt stål
MSPS2008		2200mm	26mm	800mm	2200 x 507mm	Mjukt stål
MSPS2008F		2000mm	26mm	800mm	2000 x 507mm	Mjukt stål
MSPS2203	2505147	2200mm	88.5mm	300mm	2200 x 337mm	Mjukt stål
MSPS2205	2504772	2200mm	88.5mm	500mm	2200 x 337mm	Mjukt stål
MSPS2206	2505148	2200mm	26mm	600mm	2200 x 507mm	Mjukt stål
MSPS2206F	2505043	2200mm	26mm	600mm	2200 x 507mm	Mjukt stål
MSPS2208		2200mm	26mm	800mm	2200 x 507mm	Mjukt stål

Katalognummer	E-nummer	Höjd	Bredd	Djup	Panelstorlek	Kapslingsmaterial
MSPS2208F		2200mm	26mm	800mm	2200 x 507mm	Mjukt stål

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE