

Huvudsamlingsskenan stöder horisontellt för strömdistribution, MSHS



This horizontal busbar support, MSHS, for two bars up to 120x10 mm, is available off the shelf and has been tested according to IEC 61439. It can be mounted at any height behind fix, modular, and plug-in systems.

DESIGN

Beskrivning: Busbar supports up to 3600A to be mounted horizontally behind the compartments. Mounts to the internal side panels MSPS, and in the height position which we need. Supports for single or double bar per phase for bar thickness 10 mm, and width from 10 to 120 mm. Distance between bars of 20 mm.

Material: Polycarbonate reinforced with 10% of glass material.

Leverans: Busbar support for 3 phases and neutral, and mounting material.

Distance between bars of 20 mm

Material: Polycarbonate reinforced with 10% of glass material

Delivery: Busbar support for 3 phases and neutral, and mounting material

Horizontal main busbar support for 2 bars up to 120 x 10 mm, which can be mounted at the required height behind any system (fix, modular or plug-in)

The standard supports are available off the shelf and have been tested according to IEC 61439

The supports are suitable for the most common bars on the market

Main busbars can be installed in the middle of the enclosure height, which will reduce the required busbar section

A flexible and reliable solution that ensures procurement, design and installation can be done efficiently reducing the labour time required

Internal side panels (MSPS) are required in order to mount the busbar supports

SPECIFIKATIONER

Table 1/1						
Katalognummer	E-nummer	Höjd	Bredd	Kapslingsmaterial	Produktfamilj	Material
MSHS408010	2504750	620mm	95mm	Mjukt stål	Fristående	Polykarbonat
MSHS401010	2504743	300mm	95mm	Mjukt stål	Fristående	Polykarbonat
MSHS405010	2504748	540mm	95mm	Mjukt stål	Fristående	Polykarbonat
MSHS406010	2504749	540mm	95mm	Mjukt stål	Fristående	Polykarbonat
MSHS403010	2504746	420mm	95mm	Mjukt stål	Fristående	Polykarbonat
MSHS410010	2504742	700mm	95mm	Mjukt stål	Fristående	Polykarbonat
MSHS404010	2504747	460mm	95mm	Mjukt stål	Fristående	Polykarbonat
MSHS412010	2504744	780mm	95mm	Mjukt stål	Fristående	Polykarbonat
MSHS402010	2504745	380mm	95mm	Mjukt stål	Fristående	Polykarbonat

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplikering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE