

Syspend 180-Max vertikal panelkoppling



Syspend 180-Max Vertical Panel Coupling mounts a vertical tube to the back of an enclosure or screen using Video Electronics Standards Association (VESA) mounting. The coupling has mounting holes drilled for standard VESA 75 and 100 flange sizes. It enables the enclosure to rotate 300 degrees and can be locked into a given position. The vertical panel coupling has a safety stop and maintenance-free bearings.

DESIGN

Coupling can rotate 300 degrees with stop

Gasket, set screws, and mounting hardware are included

White aluminum cable access cap is included

Assembled Syspend 180 HMI Arm System has a max weight load of 180 lb. (81.6 kg)

SPECIFIKATIONER

Material: Aluminium
Slutför: Pulverlackerad

Table 1/1						
Katalognummer	Höjd	Bredd	Djup	Färg	Färgkod	Tjocklek
S1MPCVG	185mm	120mm	140mm	Ljusgrå	RAL 7035	5.5mm
S1MPCV	256mm	140mm	120mm	Kolsvart	RAL 9005	5.5mm

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:
CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE