

Syspend 281-Max 48-mm rund rörflänskoppling och adapter



Syspend 281-Max 48-mm Round Tube Flange Coupling attaches the Vertical Motion Pedestal Tube or any 48-mm round tube to the enclosure. Enclosure can be rotated 300 degrees and locked in position. Includes safety stop and maintenance-free bearing.

Syspend 281-Max Adapter is required to attach the Flange Coupling to a standard HOFFMAN HMI enclosure that uses a 60 x 60-mm hole pattern (i.e. Syspend Aluminum HMI and Concept HMI). Adapter is not required as the Coupling attaches to enclosure using a 48 x 48-mm hole pattern directly.

DESIGN

Gasket and mounting hardware are included

Assembled Syspend 281 HMI Arm System has a max weight load of 281 lb. (127.7 kg)

SPECIFIKATIONER

Material: Aluminium
Färg: Kolsvart
Slutför: Pulverlackerad
Färgkod: RAL 9005

Table 1/1				
Katalognummer	Höjd	Bredd	Djup	Snabbleverans
S2MA48	15mm	80mm	80mm	Nej
S2MFC48	127mm	80mm	80mm	Nej

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:
CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE