

Roterande basfäste, S2MRB



Suspend 281-Max Rotary Base allows the entire suspension system to rotate at the point of attachment on a horizontal surface. Arm can be rotated or turned 300 degrees. Includes safety stop and maintenance-free bearing.

DESIGN

Set screws and gasket are included

Surface mounting fasteners are not provided

Assembled Suspend 281 HMI Arm System has a max weight load of 281 lb. (127.7 kg)

SPECIFIKATIONER

Table 1/1						
Katalognummer	Höjd	Bredd	Djup	Material	Yta	Färg
S2MRB	167mm	125mm	125mm	Aluminium	Pulverlackerad	Jet Black

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE