

T-koppling utanför övre öppning, infästning med gångjärn



Lay-in Hinged Cover Tee Fitting with Outside Top Opening is used when the covers of two branches are on the same side and the third is on a different side.

BRANSCHSTANDARDER

Certified by Canadian Standards Association.

DESIGN

Lay-in Hinged Cover Tee Fitting with Outside Top Opening is used when the covers of two branches are on the same side and the third is on a different side

SPECIFIKATIONER

Färgkod: ANSI 61
Slutför: Galvaniserad; Pulverlackerad
Färg: Grå
Material: Mjukt stål

Table 1/1

Katalognummer	Typ	Höjd	Bredd	Tjocklek	Typ av tätningsplatta	Tätningsplatta antal
F44LTC	Tee	102mm	102mm	1.9mm	Platt	2
F88LTC	Tee	203mm	203mm	1.9mm	Platt	2
F66LTC	Tee	152mm	152mm	1.9mm	Platt	2
F22LTC	Tee	64mm	64mm	1.9mm	Platt	2

YTTERLIGARE PRODUKTINFORMATION

Each sealing plate also includes one gasket and one set of screws to join sections.

Certified by Canadian Standards Association.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE