

# Universal Busbar stöder, EUBS



This busbar support, EUBS, is available for one, two, or three bars up to 120 x 10 mm. The support can be mounted either at the top or bottom of the enclosure. It is available off the shelf and tested according to IEC 61439. This support is required when a high level of mounting flexibility is required.

## DESIGN

Description: Busbar support up to 4500A to be mounted horizontally or vertically. Mounts directly to the enclosure frame or with help of CLPF profiles. Available in one/two/three bars per phase for bar thickness 10 mm, and width from 30 to 120 mm.

Working temperature: -40°C up to 130°C.

Material: Reinforced polyamide and steel. Halogen free.

Delivery: Busbar support with mounting material.

## SPECIFIKATIONER

Table 1/1

| Katalognummer | E-nummer | Samlingsskenans tjocklek | Samlingsskenor per fas | Samlingsskenans bredd | Material       | Slutför   |
|---------------|----------|--------------------------|------------------------|-----------------------|----------------|-----------|
| EUBS310TN     | 2505054  | 10mm min                 | 3Ph min                | 30 – 125mm            | Stål, Polyamid | Pläterade |
| EUBS110TN     | 2505052  | 10mm min                 | 1Ph min                | 30 – 125mm            | Stål, Polyamid | Pläterade |
| EUBS210TN     | 2505053  | 10mm min                 | 2Ph min                | 30 – 125mm            | Stål, Polyamid | Pläterade |

## VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på [www.nvent.com](http://www.nvent.com) och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE