


Vertical rear busbar supports | Strömfördelning, MSFH



This fix system vertical busbar support, MSFH, for two bars up to 40 x 10 mm, is available off the shelf and has been tested according to IEC 61439.

DESIGN

Beskrivning: Busbar supports up to 1600A to be mounted vertically behind the fixed compartments. Mounts to the vertical profiles MSFP. Rated short-time withstand current up to 35 kA with rear supports and up to 50 kA with rear and front supports.

Material: Polycarbonate reinforced with 10% of glass material.

Leverans: 7 busbar supports for 3 phases and neutral, and mounting material.

A flexible and reliable solution that ensures procurement, design and installation can be done efficiently reducing the labour time required

Fix system vertical profiles (MSFP) are required in order to mount the busbar supports

Busbar supports up to 1600A to be mounted vertically behind the fixed compartments

Mounts to the vertical profiles MSFP

Rated short-time withstand current up to 35 kA with rear supports and up to 50 kA with rear and front supports

Delivery: 7 busbar supports for 3 phases and neutral, and mounting material

SPECIFIKATIONER

Table 1/1						
Katalognummer	E-nummer	Höjd	Bredd	Djup	Skåpmaterial	Produktfamilj
MSFH06	2505159	40mm	600mm	45mm	Stålplåt	Fristående

YTTERLIGARE PRODUKTINFORMATION

*In: Rated current. *Icw: Rated short-time withstand current.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE