

nVent LENTON Interlok HY15LM Grout



The nVent LENTON Interlok HY15LM grout is a proprietary, nonmetallic, high-strength, nonshrink grout developed exclusively for the nVent LENTON Interlok coupling system. The nVent LENTON Interlok HY15LM grout is produced under strict nVent quality guidelines in order to ensure product quality along with consistent and reliable performance.

CERTIFIERINGAR



DESIGN

Cures quickly, allowing early removal of bracing systems

Nonmetallic grout will not rust or stain structures

Designed to provide superior dynamic, seismic and ultimate strength performance for moment frame applications

For use in pump or gravity fill applications

SPECIFIKATIONER

Table 1/1

Katalognummer	Tryckhållfasthet	Arbetstemperatur	Enhetsvikt
HY15LM	24.1 MPa @ 1 d, 110.3 MPa @ 28 d	0 to 38 °C	22.68 kg

YTTERLIGARE PRODUKTINFORMATION

Compressive Strength is based on room temperature tests performed at 70°F (21°C).

The shelf life of nVent LENTON Interlok Grout is 12 months from the manufacturing date printed on the bag.

nVent LENTON Interlok Grout should be stored in a cool, dry environment. It is recommended that the nVent LENTON Interlok Grout be stored indoors to maintain maximum shelf life and physical properties.

Prior to installation, please read and understand the detailed instructions and safety notices provided in the nVent LENTON Interlok Instruction Manual.

Part Number	Article Number	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Number of Couplers Per Bag of LENTON INTERLOK Grout
LK5	145575	16 mm	#5	15M	24
LK6	145580	20 mm	#6	20M	25
LK7	145585	22 mm	#7	-	26
LK8	145590	25 mm	#8	25M	21
LK9	145595	28 mm	#9	30M	17
LK10	145600	32 mm	#10	-	13.5
LK11	145605	36 mm	#11	35M	11.5
LK40	145610	40 mm	-	-	7
LKT14	145611	43 mm	#14	45M	7
LKT50	145615	50 mm	-	-	4
LKT18	145620	57 mm	#18	55M	4.5

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Vårt starka utbud av varumärken:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE