

19" Fan Unit, 1 U, Remote Control and Monitoring

Energiföretag

Fan Unit with ModBus interface for installation into a 1 U space within the Cabinet

FUNKTIONER

Fan speed temperature controlled

ModBus Interface for Remote Monitoring and Control

Temperature threshold for the fan control adjustable on the front panel

Signaling of fan failure and over temperature by 2 LEDs and potential-free relay outputs

Integrated power supply with wide range input (100 V – 240 V)

Less than 1 U (42 mm) to enable mounting on sliding guide rails or drawer

2 NTC temperature sensors with Cables included

SPECIFIKATIONER

Table 1/2

Katalognummer	Input Voltage AC	Airflow	Noise Level	Elförsörjning	Max Static Pressure	Omgivningstemperatur
10713-554	100 – 240 V	1089 m ³ /h	59.5 dB(A)	97 W	78 Pa	–10 to 70 °C

Table 2/2

Katalognummer	Lifespan, L10 @ 40 C
10713-554	99558 h

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE