

19" Fan Unit, 1 U, Speed Control and Monitoring

Energiföretag

Fan Unit for installation into a 1 U space within the Cabinet.



CERTIFIERING



FUNKTIONER

Range selectable: 20 ... 40 °C and 30 ... 50 °C

Low noise through temperature dependent air flow

External sensor, max speed is default failure state

Function control with LEDs and via dry contact

Contact protection in accordance with DIN EN ISO 13857

SPECIFIKATIONER

Table 1/1

Katalognummer	Input Voltage AC	Input Voltage DC	Certifiering
10713-098		24 V min	RoHS, CE, EAC
10713-099		24 V min	RoHS, CE, EAC

Katalognummer	Input Voltage AC	Input Voltage DC	Certifiering
19713-006	230 V min		RoHS, EAC
19713-121	230 V min		RoHS, EAC

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE