

Varistar CP Seismic Base/Plinth, 103H 800W 600D

Energiföretag

KATALOGNUMMER

21630-115

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.

FUNKTIONER

2 support profiles, St, 10 mm, side

Seismic dynamic load-carrying capacity 500 kg

Height 103 mm

2 covers, St, 10 mm, front and rear

Conforms to NEBS, Earthquake secure (up) to Bellcore Zone 4, tested with 500 KGs, Mounting holes for fitting of base

Access possible from front and rear

PRODUKTATTRIBUT

Product Type: Cabinet/Rack Base

Product Family: Varistar CP

Type: Base Plinth

Material: Stål

Color: Black Grey

Color Code: RAL 7021

Height: 103 mm

Width: 800 mm

Depth: 800 mm

Complies With: IEC 61587-1; IEC 61587-2

Static Load: 400 N

Works With: Varistar CP

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE