

Varistar CP Steel Door, Perforated With 1-Point Locking, Key Plate Only, RAL 7021, 29 U, 1400H 800W

Power Utilities

KATALOGNUMMER

21630-510



Varistar CP Perforated Steel Door Single Point Locking for IP 20 applications.

DESIGN

Perforated steel door with single point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

Key lock cover

PRODUKTATTRIBUT

Produkttyp: Skåpdörr

Produktfamilj: Varistar CP

Typ: Ståldörr, perforerad

Fungerar med.: Varistar CP

Låstyp: Enpunktslås

Färg: Svart grå

Färgkod: RAL 7021

Rackhöjd: 29 U

Höjd: 1400 mm

Bredd: 800 mm

Skyddsklass: IP20

Överensstämmer med.: IEC 61587-1

YTTERLIGARE PRODUKTINFORMATION

Please order lever handle and DIN profile half cylinder separately.

Please purchase the grounding kit separately.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE