


RackPower iPDU, RP1326, 100-240 VAC, 1-phase

Energiföretag

KATALOGNUMMER

RP1326



Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design with only 44 mm height.

FUNKTIONER

RackPower RP1xxx Intelligent Power Distribution Units monitors input power of the entire PDU, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 100 - 240 VAC, 1-phase L-N or L-L

Input connector C20

C13, C19 outlets

PRODUKTATTRIBUT

Product Type: Socket Strip

Socket Type: IEC C13; IEC C19

Color: Svart

Length: 1490 mm

Voltage AC: 208 V

Function: Input Monitored

Depth: 53 mm

Width: 52 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE