

EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding, Front Handle

Energiföretag

Non-EMC shielded subrack for backplane mounting, heavy version with tox welded side panels and front handle.



CERTIFIERING



FUNKTIONER

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Supplied as space-saving flat-pack

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version with front handles

SPECIFIKATIONER

Table 1/3

Katalognummer	Rack Height	Djup	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24567-161	3 U	175 mm	1	Backplane	160 mm	Rostfritt stål
24567-162	3 U	235 mm	1	Backplane	160 mm, 220 mm	Rostfritt stål
24567-163	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Rostfritt stål
24567-164	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Rostfritt stål
24567-461	6 U	175 mm	1	Backplane	160 mm	Rostfritt stål
24567-462	6 U	235 mm	1	Backplane	160 mm, 220 mm	Rostfritt stål
24567-463	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Rostfritt stål
24567-464	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Rostfritt stål

Table 2/3

Katalognummer	Shock and Vibration Tolerance	Handle Included	Montering	Uppfyller kraven enligt	EMC Shielding	Product Type
24567-161	5 g (force)	Ja	Rack	IEC 60297-3-103	Nej	Subrack/Chassis
24567-162	5 g (force)	Ja	Rack	IEC 60297-3-103	Nej	Subrack/Chassis
24567-163	5 g (force)	Ja	Rack	IEC 60297-3-103	Nej	Subrack/Chassis
24567-164	5 g (force)	Ja	Rack	IEC 60297-3-103	Nej	Subrack/Chassis
24567-461	5 g (force)	Ja	Rack	IEC 60297-3-103	Nej	Subrack/Chassis
24567-462	5 g (force)	Ja	Rack	IEC 60297-3-103	Nej	Subrack/Chassis

Katalognummer	Shock and Vibration Tolerance	HandleIncluded	Montering	Uppfyller kraven enligt	EMC Shielding	Product Type
24567-463	5 g (force)	Ja	Rack	IEC 60297-3-103	Nej	Subrack/Chassis
24567-464	5 g (force)	Ja	Rack	IEC 60297-3-103	Nej	Subrack/Chassis

Table 3/3

Katalognummer	Rack Width	Statisk belastning	Certifiering
24567-161	84 HP	15 kgf	RoHS
24567-162	84 HP	15 kgf	RoHS, DB
24567-163	84 HP	15 kgf	RoHS, DB
24567-164	84 HP	15 kgf	RoHS, DB
24567-461	84 HP	15 kgf	RoHS, DB
24567-462	84 HP	15 kgf	RoHS, DB
24567-463	84 HP	15 kgf	RoHS, DB
24567-464	84 HP	15 kgf	RoHS, DB

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE