

EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding

Energiföretag

Rear horizontal rail for backplane mounting with insulation strip



CERTIFIERING



FUNKTIONER

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version without front handles

Supplied as space-saving flat-pack

SPECIFIKATIONER

Table 1/3

Katalognummer	Rack Height	Djup	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-161	3 U	175 mm	1	Backplane	160 mm	Textile
24563-162	3 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-163	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-164	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Textile
24563-461	6 U	175 mm	1	Backplane	160 mm	Textile
24563-462	6 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-463	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-464	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Textile

Table 2/3

Katalognummer	Shock and Vibration Tolerance	Handle Included	Montering	Uppfyller kraven enligt	EMC Shielding	Product Type
24563-161	5 g (force)	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis
24563-162	5 g (force)	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis
24563-163	5 g (force)	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis
24563-164	5 g (force)	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis
24563-461	5 g (force)	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis
24563-462	5 g (force)	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis
24563-463	5 g (force)	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis

Katalognummer	Shock and Vibration Tolerance	HandleIncluded	Montering	Uppfyller kraven enligt	EMC Shielding	Product Type
24563-464	5 g (force)	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis

Table 3/3

Katalognummer	Rack Width	Statisk belastning
24563-161	84 HP	15 kgf
24563-162	84 HP	15 kgf
24563-163	84 HP	15 kgf
24563-164	84 HP	15 kgf
24563-461	84 HP	15 kgf
24563-462	84 HP	15 kgf
24563-463	84 HP	15 kgf
24563-464	84 HP	15 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE