

EuropacPRO 19" Subrack Kit for Backplane, Light, Unshielded

Power Utilities

Non-EMC shielded subrack for backplane mounting, light version.



CERTIFIERINGAR



DESIGN

Subrack with side panel type L ("light") with integrated 19" support brackets

Horizontal rail type "light"

Aluminum construction

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 7.5 kg

Supplied as space-saving flat-pack

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Modifications such as cutouts, different finishes or dimensions available

SPECIFIKATIONER

Table 1/2

Katalognummer	Rackhöjd	Djup	Förpackningskvantitet	För montering	Kortdjup	Handtag medföljer
24564-433	6 U	295 mm	1	Bakplan	160 mm, 220 mm, 280 mm	Nej
24564-432	6 U	235 mm	1	Bakplan	160 mm, 220 mm	Nej
24564-431	6 U	175 mm	1	Bakplan	160 mm	Nej
24564-133	3 U	295 mm	1	Bakplan	160 mm, 220 mm, 280 mm	Nej
24564-132	3 U	235 mm	1	Bakplan	160 mm, 220 mm	Nej
24564-131	3 U	175 mm	1	Bakplan	160 mm	Nej

Table 2/2

Katalognummer	Montering	Överensstämmer med.	EMC-skärmning	Produkttyp	Rackbredd	Statisk belastning
24564-433	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	Nej	Subrack/chassi	84 HP	7.5 kgf
24564-432	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	Nej	Subrack/chassi	84 HP	7.5 kgf
24564-431	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	Nej	Subrack/chassi	84 HP	7.5 kgf
24564-133	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	Nej	Subrack/chassi	84 HP	7.5 kgf
24564-132	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	Nej	Subrack/chassi	84 HP	7.5 kgf
24564-131	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	Nej	Subrack/chassi	84 HP	7.5 kgf

YTTERLIGARE PRODUKTINFORMATION

Subrack is not prepared for shielding, retrofit for protection class IP 20 possible

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE