

EuropacPRO 19" Subrack Kit for Backplane, Retrofit Shielding

Energiföretag

Non-shielded subrack for backplane mounting.



CERTIFIERING



FUNKTIONER

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Rear horizontal rail for backplane mounting with insulation strip

Aluminum construction

IP 20, in accordance with IEC 60529

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

SPECIFIKATIONER

Table 1/3

Katalognummer	Rack Height	Djup	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-131	3 U	175 mm	1	Backplane	160 mm	Rostfritt stål
24563-132	3 U	235 mm	1	Backplane	160 mm, 220 mm	Rostfritt stål
24563-133	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Rostfritt stål
24563-134	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Rostfritt stål
24563-135	3 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Rostfritt stål
24563-136	3 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Rostfritt stål
24563-431	6 U	175 mm	1	Backplane	160 mm	Rostfritt stål
24563-432	6 U	235 mm	1	Backplane	160 mm, 220 mm	Rostfritt stål
24563-433	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Rostfritt stål
24563-434	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Rostfritt stål
24563-435	6 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Rostfritt stål
24563-436	6 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Rostfritt stål

Table 2/3

Katalognummer	Handle Included	Montering	Uppfyller kraven enligt	EMC Shielding	Product Type	Rack Width
24563-131	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis	84 HP
24563-132	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis	84 HP

Katalognummer	HandleIncluded	Montering	Uppfyller kraven enligt	EMC Shielding	Product Type	Rack Width
24563-133	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis	84 HP
24563-134	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis	84 HP
24563-135	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis	84 HP
24563-136	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis	84 HP
24563-431	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis	84 HP
24563-432	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis	84 HP
24563-433	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis	84 HP
24563-434	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis	84 HP
24563-435	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis	84 HP
24563-436	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis	84 HP

Table 3/3

Katalognummer	Statisk belastning
24563-131	11 kgf
24563-132	11 kgf
24563-133	11 kgf
24563-134	11 kgf
24563-135	11 kgf
24563-136	11 kgf
24563-431	11 kgf

Katalognummer	Statisk belastning
24563-432	11 kgf
24563-433	11 kgf
24563-434	11 kgf
24563-435	11 kgf
24563-436	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE