

EuropacPRO 19" Subrack Kit for Backplane, Shielded, CompactPCI

Energiföretag

EMC Shielded subrack for backplane mounting, for CPCI application.

CERTIFIERING



FUNKTIONER

Subrack with side panel type F ("flexible") for CompactPCI plug-in units with high insertion and withdrawal forces

Aluminum construction

Rear horizontal rail for backplane mounting with insulation strip

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, -102, -103, -104, IEEE 1101.1, IEEE 1101.10/11

Modifications such as cutouts, different finishes or dimensions available

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Supplied as space-saving flat-pack

IP 20, in accordance with IEC 60529

Horizontal rail type "Heavy"

SPECIFIKATIONER

Table 1/3

Katalognummer	Rack Height	Djup	Rear I/O	Package Quantity	For Mounting	Board Depth
24563-152	3 U	235 mm		1	Backplane	160 mm

Katalognummer	Rack Height	Djup	Rear I/O	Package Quantity	For Mounting	Board Depth
24563-157	3 U	275 mm	Ja	1	Backplane	80 mm, 160 mm
24563-452	6 U	235 mm		1	Backplane	160 mm
24563-457	6 U	275 mm	Ja	1	Backplane	80 mm, 160 mm

Table 2/3

Katalognummer	EMC Gasket Type	Handle Included	Montering	Uppfyller kraven enligt	EMC Shielding	Product Type
24563-152	Textile	Nej	Rack	IEC 60297-3-103, IEEE 1101.10	Ja	Subrack/Chassis
24563-157	Textile	Nej	Rack	IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11	Ja	Subrack/Chassis
24563-452	Textile	Nej	Rack	IEC 60297-3-103, IEEE 1101.10	Ja	Subrack/Chassis
24563-457	Textile	Nej	Rack	IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11	Ja	Subrack/Chassis

Table 3/3

Katalognummer	Rack Width	Statisk belastning
24563-152	84 HP	11 kgf
24563-157	84 HP	11 kgf
24563-452	84 HP	11 kgf
24563-457	84 HP	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE