

# EuropacPRO 19" Subrack Kit for DIN Connector, Retrofit Shielding

## Energiföretag

Non-shielded subrack for Din Connector mounting EN 60603-2 (DIN 41612).



## CERTIFIERING



## FUNKTIONER

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Aluminum construction

IP 20, in accordance with IEC 60529

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rails for connector mounting (IEC 60603-2 / DIN 41612)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

## SPECIFIKATIONER

Table 1/3

| Katalognummer | Rack Height | Djup   | Package Quantity | For Mounting  | Board Depth                    | EMC Gasket Type |
|---------------|-------------|--------|------------------|---------------|--------------------------------|-----------------|
| 24563-191     | 3 U         | 175 mm | 1                | DIN Connector | 160 mm                         | Rostfritt stål  |
| 24563-192     | 3 U         | 235 mm | 1                | DIN Connector | 160 mm, 220 mm                 | Rostfritt stål  |
| 24563-193     | 3 U         | 295 mm | 1                | DIN Connector | 160 mm, 220 mm, 280 mm         | Rostfritt stål  |
| 24563-194     | 3 U         | 355 mm | 1                | DIN Connector | 160 mm, 220 mm, 280 mm, 340 mm | Rostfritt stål  |
| 24563-491     | 6 U         | 175 mm | 1                | DIN Connector | 160 mm                         | Rostfritt stål  |
| 24563-492     | 6 U         | 235 mm | 1                | DIN Connector | 160 mm, 220 mm                 | Rostfritt stål  |
| 24563-493     | 6 U         | 295 mm | 1                | DIN Connector | 160 mm, 220 mm, 280 mm         | Rostfritt stål  |
| 24563-494     | 6 U         | 355 mm | 1                | DIN Connector | 160 mm, 220 mm, 280 mm, 340 mm | Rostfritt stål  |

Table 2/3

| Katalognummer | Handle Included | Montering | Uppfyller kraven enligt | EMC Shielding | Product Type    | Rack Width |
|---------------|-----------------|-----------|-------------------------|---------------|-----------------|------------|
| 24563-191     | Nej             | Rack      | IEC 60297-3-103         | Nej           | Subrack/Chassis | 84 HP      |
| 24563-192     | Nej             | Rack      | IEC 60297-3-103         | Nej           | Subrack/Chassis | 84 HP      |
| 24563-193     | Nej             | Rack      | IEC 60297-3-103         | Nej           | Subrack/Chassis | 84 HP      |
| 24563-194     | Nej             | Rack      | IEC 60297-3-103         | Nej           | Subrack/Chassis | 84 HP      |
| 24563-491     | Nej             | Rack      | IEC 60297-3-103         | Nej           | Subrack/Chassis | 84 HP      |
| 24563-492     | Nej             | Rack      | IEC 60297-3-103         | Nej           | Subrack/Chassis | 84 HP      |
| 24563-493     | Nej             | Rack      | IEC 60297-3-103         | Nej           | Subrack/Chassis | 84 HP      |

| Katalognummer | HandleIncluded | Montering | Uppfyller kraven enligt | EMC Shielding | Product Type    | Rack Width |
|---------------|----------------|-----------|-------------------------|---------------|-----------------|------------|
| 24563-494     | Nej            | Rack      | IEC 60297-3-103         | Nej           | Subrack/Chassis | 84 HP      |

Table 3/3

| Katalognummer | Statisk belastning |
|---------------|--------------------|
| 24563-191     | 11 kgf             |
| 24563-192     | 11 kgf             |
| 24563-193     | 11 kgf             |
| 24563-194     | 11 kgf             |
| 24563-491     | 11 kgf             |
| 24563-492     | 11 kgf             |
| 24563-493     | 11 kgf             |
| 24563-494     | 11 kgf             |

## ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på [www.nvent.com](http://www.nvent.com) och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**