

EuropacPRO Rugged Rear Angle for Textile EMC Gasket

Energiföretag



Corner profile covers the slot between the side panel and the rear panel of a subrack. Needed for a proper EMC shielding.

CERTIFIERING



FUNKTIONER

Required for shielding of rear

Can also be used as front closure when using a depth-adjustable 19" support bracket

SPECIFIKATIONER

Table 1/2

Katalognummer	Rack Height	Package Quantity	Höjd	Product Family	Product Type	Typ
24566-197	3 U	1	132.6 mm	EuropacPRO	Skydd	Rugged
24566-199	3 U	1	132.6 mm	EuropacPRO	Skydd	Rugged

Katalognummer	Rack Height	Package Quantity	Höjd	Product Family	Product Type	Typ
24566-497	6 U	1	265.9 mm	EuropacPRO	Skydd	Rugged
24566-499	6 U	1	265.9 mm	EuropacPRO	Skydd	Rugged

Table 2/2

Katalognummer	Fungerar med	Förpackningsenhet	Certifiering
24566-197	Subracks	Par	
24566-199	Subracks	Par	RoHS
24566-497	Subracks	Par	
24566-499	Subracks	Par	RoHS

ADDITIONAL PRODUCT DETAILS

Please order EMC textile gasket separately.

Corner profile cannot be used together with adapter for rear mounting.

WARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE