

Front Panel, Anodized With Untreated Edges, Unshielded

Energiföretag



Front Panel, anodized with untreated edges, unshielded. The panels enable mounting on horizontal rails.

CERTIFIERING



FUNKTIONER

Partial width front panel, Al, 2.5 mm

Al, clear anodized, untreated edges

SPECIFIKATIONER

Table 1/3

Katalognummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montering	Front Finish
30818-271	2 U	84 HP	1	Ingen	Screw-on Front	Anodized
30818-310	3 U	42 HP	1	Ingen	Screw-on Front	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montering	Front Finish
30818-331	3 U	63 HP	1	Ingen	Screw-on Front	Anodized
30818-352	3 U	84 HP	1	Ingen	Screw-on Front	Anodized
30818-434	4 U	84 HP	1	Ingen	Screw-on Front	Anodized
30818-556	6 U	42 HP	1	Ingen	Screw-on Front	Anodized
30818-577	6 U	63 HP	1	Ingen	Screw-on Front	Anodized
30818-598	6 U	84 HP	1	Ingen	Screw-on Front	Anodized
30810-433	3 U	2 HP	5	Ingen	Screw-on Front	Anodized
30818-747	6 U	2 HP	5	Ingen	Screw-on Front	Anodized
30818-272	3 U	3 HP	5	Ingen	Screw-on Front	Anodized
30818-273	3 U	4 HP	5	Ingen	Screw-on Front	Anodized
30818-274	3 U	5 HP	5	Ingen	Screw-on Front	Anodized
30818-275	3 U	6 HP	5	Ingen	Screw-on Front	Anodized
30818-276	3 U	7 HP	5	Ingen	Screw-on Front	Anodized
30818-277	3 U	8 HP	5	Ingen	Screw-on Front	Anodized
30818-279	3 U	10 HP	5	Ingen	Screw-on Front	Anodized
30818-281	3 U	12 HP	5	Ingen	Screw-on Front	Anodized
30818-282	3 U	14 HP	5	Ingen	Screw-on Front	Anodized
30818-284	3 U	16 HP		Ingen	Screw-on Front	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Handle Type	Montering	Front Finish
30818-289	3 U	21 HP	5	Ingen	Screw-on Front	Anodized
30818-296	3 U	28 HP	5	Ingen	Screw-on Front	Anodized
30818-517	6 U	3 HP		Ingen	Screw-on Front	Anodized
30818-518	6 U	4 HP	5	Ingen	Screw-on Front	Anodized
30818-519	6 U	5 HP	5	Ingen	Screw-on Front	Anodized
30818-520	6 U	6 HP	5	Ingen	Screw-on Front	Anodized
30818-521	6 U	7 HP	5	Ingen	Screw-on Front	Anodized
30818-522	6 U	8 HP	5	Ingen	Screw-on Front	Anodized
30818-524	6 U	10 HP	5	Ingen	Screw-on Front	Anodized
30818-526	6 U	12 HP	5	Ingen	Screw-on Front	Anodized
30818-528	6 U	14 HP	5	Ingen	Screw-on Front	Anodized
30818-530	6 U	16 HP	5	Ingen	Screw-on Front	Anodized
30818-535	6 U	21 HP	5	Ingen	Screw-on Front	Anodized
30818-542	6 U	28 HP	5	Ingen	Screw-on Front	Anodized

Table 2/3

Katalognummer	Rear Finish	Treated Edges	Uppfyller kraven enligt	EMC Shielding	Höjd	Material
30818-271	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	84 mm	Aluminium
30818-310	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Uppfyller kraven enligt	EMC Shielding	Höjd	Material
30818-331	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium
30818-352	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium
30818-434	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	172.9 mm	Aluminium
30818-556	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	261.8 mm	Aluminium
30818-577	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	261.8 mm	Aluminium
30818-598	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	261.8 mm	Aluminium
30810-433	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium
30818-747	Anodized	Ja	IEC 60297-3-101, IEEE 1101.1/10	Nej	261.8 mm	Aluminium
30818-272	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium
30818-273	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium
30818-274	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium
30818-275	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium
30818-276	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium
30818-277	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Uppfyller kraven enligt	EMC Shielding	Höjd	Material
30818-279	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium
30818-281	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium
30818-282	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium
30818-284	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium
30818-289	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium
30818-296	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium
30818-517	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	261.8 mm	Aluminium
30818-518	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	261.8 mm	Aluminium
30818-519	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	261.8 mm	Aluminium
30818-520	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	261.8 mm	Aluminium
30818-521	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	261.8 mm	Aluminium
30818-522	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	261.8 mm	Aluminium
30818-524	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	261.8 mm	Aluminium
30818-526	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	261.8 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Uppfyller kraven enligt	EMC Shielding	Höjd	Material
30818-528	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	261.8 mm	Aluminium
30818-530	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	261.8 mm	Aluminium
30818-535	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	261.8 mm	Aluminium
30818-542	Anodized	Nej	IEC 60297-3-101, IEEE 1101.1/10	Nej	261.8 mm	Aluminium

Table 3/3

Katalognummer	Product Type	Typ	Bredd	Certifiering
30818-271	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30818-310	Front Panel	Front Panel without Handle	213 mm	RoHS
30818-331	Front Panel	Front Panel without Handle	319.7 mm	RoHS
30818-352	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30818-434	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30818-556	Front Panel	Front Panel without Handle	213 mm	RoHS
30818-577	Front Panel	Front Panel without Handle	319.7 mm	RoHS
30818-598	Front Panel	Front Panel without Handle	426.4 mm	RoHS
30810-433	Front Panel	Front Panel without Handle	9.8 mm	RoHS
30818-747	Front Panel	Front Panel without Handle	9.8 mm	RoHS
30818-272	Front Panel	Front Panel without Handle	14.9 mm	RoHS
30818-273	Front Panel	Front Panel without Handle	20 mm	RoHS

Katalognummer	Product Type	Typ	Bredd	Certifiering
30818-274	Front Panel	Front Panel without Handle	25 mm	RoHS
30818-275	Front Panel	Front Panel without Handle	30.1 mm	RoHS
30818-276	Front Panel	Front Panel without Handle	35.2 mm	RoHS
30818-277	Front Panel	Front Panel without Handle	40.3 mm	RoHS
30818-279	Front Panel	Front Panel without Handle	50.5 mm	RoHS
30818-281	Front Panel	Front Panel without Handle	60.6 mm	RoHS
30818-282	Front Panel	Front Panel without Handle	70.8 mm	RoHS
30818-284	Front Panel	Front Panel without Handle	80.9 mm	
30818-289	Front Panel	Front Panel without Handle	106.3 mm	RoHS
30818-296	Front Panel	Front Panel without Handle	141.9 mm	RoHS
30818-517	Front Panel	Front Panel without Handle	14.9 mm	
30818-518	Front Panel	Front Panel without Handle	20 mm	RoHS
30818-519	Front Panel	Front Panel without Handle	25 mm	RoHS
30818-520	Front Panel	Front Panel without Handle	30.1 mm	RoHS
30818-521	Front Panel	Front Panel without Handle	35.2 mm	RoHS
30818-522	Front Panel	Front Panel without Handle	40.3 mm	RoHS
30818-524	Front Panel	Front Panel without Handle	50.5 mm	RoHS
30818-526	Front Panel	Front Panel without Handle	60.6 mm	RoHS

Katalognummer	Product Type	Typ	Bredd	Certifiering
30818-528	Front Panel	Front Panel without Handle	70.8 mm	RoHS
30818-530	Front Panel	Front Panel without Handle	80.9 mm	RoHS
30818-535	Front Panel	Front Panel without Handle	106.3 mm	RoHS
30818-542	Front Panel	Front Panel without Handle	141.9 mm	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE