

Front Panel, Refrofit Shielding

Energiföretag



Flat front panel. Shieldable with stainless steel EMC gasket.

CERTIFIERING



FUNKTIONER

For stainless steel EMC gasket

Aluminum, 2.5 mm, front anodized, conductive

SPECIFIKATIONER

Table 1/3

Katalognummer	Rack Height	Rack Width	Package Quantity	Montering	EMC Gasket Type	Front Finish
20846-437	3 U	42 HP	1	Screw-on Front	Rostfritt stål	Anodized
20846-438	3 U	63 HP	1	Screw-on Front	Rostfritt stål	Anodized
20846-453	6 U	42 HP	1	Screw-on Front	Rostfritt stål	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Montering	EMC Gasket Type	Front Finish
20846-454	6 U	63 HP	1	Screw-on Front	Rostfritt stål	Anodized
30846-676	3 U	84 HP	1	Screw-on Front	Rostfritt stål	Anodized
30846-683	4 U	84 HP	1	Screw-on Front	Rostfritt stål	Anodized
30846-771	6 U	84 HP	1	Screw-on Front	Rostfritt stål	Anodized
30846-859	9 U	84 HP	1	Screw-on Front	Rostfritt stål	Anodized
30846-588	2 U	84 HP	1	Screw-on Front	Rostfritt stål	Anodized
30846-864	3 U	2 HP	5	Screw-on Front	Rostfritt stål	Anodized
30846-865	6 U	2 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-424	3 U	16 HP		Screw-on Front	Rostfritt stål	Anodized
20846-425	3 U	3 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-426	3 U	4 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-427	3 U	5 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-428	3 U	6 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-429	3 U	7 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-430	3 U	8 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-431	3 U	10 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-432	3 U	12 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-433	3 U	14 HP	5	Screw-on Front	Rostfritt stål	Anodized

Katalognummer	Rack Height	Rack Width	Package Quantity	Montering	EMC Gasket Type	Front Finish
20846-434	3 U	21 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-436	3 U	28 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-442	6 U	3 HP		Screw-on Front	Rostfritt stål	Anodized
20846-443	6 U	4 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-444	6 U	5 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-445	6 U	6 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-446	6 U	7 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-447	6 U	8 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-448	6 U	10 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-449	6 U	12 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-450	6 U	14 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-451	6 U	21 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-452	6 U	28 HP	5	Screw-on Front	Rostfritt stål	Anodized
20846-456	6 U	16 HP	5	Screw-on Front	Rostfritt stål	Anodized

Table 2/3

Katalognummer	Rear Finish	Treated Edges	Uppfyller kraven enligt	EMC Shielding	Höjd	Material
20846-437	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-438	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Uppfyller kraven enligt	EMC Shielding	Höjd	Material
20846-453	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-454	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
30846-676	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
30846-683	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	172.9 mm	Aluminium
30846-771	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
30846-859	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	395.1 mm	Aluminium
30846-588	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	84 mm	Aluminium
30846-864	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
30846-865	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-424	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-425	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-426	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-427	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-428	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Uppfyller kraven enligt	EMC Shielding	Höjd	Material
20846-429	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-430	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-431	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-432	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-433	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-434	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-436	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	128.4 mm	Aluminium
20846-442	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-443	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-444	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-445	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-446	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-447	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-448	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium

Katalognummer	Rear Finish	Treated Edges	Uppfyller kraven enligt	EMC Shielding	Höjd	Material
20846-449	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-450	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-451	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-452	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium
20846-456	Conductive	Nej	IEC 60297-3-101, IEEE 1101.1/10	No (Retrofittable)	261.8 mm	Aluminium

Table 3/3

Katalognummer	Product Type	Typ	Bredd
20846-437	Front Panel	Front Panel without Handle	213 mm
20846-438	Front Panel	Front Panel without Handle	319.7 mm
20846-453	Front Panel	Front Panel without Handle	213 mm
20846-454	Front Panel	Front Panel without Handle	319.7 mm
30846-676	Front Panel	Front Panel without Handle	426.4 mm
30846-683	Front Panel	Front Panel without Handle	426.4 mm
30846-771	Front Panel	Front Panel without Handle	426.4 mm
30846-859	Front Panel	Front Panel without Handle	426.4 mm
30846-588	Front Panel	Front Panel without Handle	426.4 mm
30846-864	Front Panel	Front Panel without Handle	9.8 mm

Katalognummer	Product Type	Typ	Bredd
30846-865	Front Panel	Front Panel without Handle	9.8 mm
20846-424	Front Panel	Front Panel without Handle	80.9 mm
20846-425	Front Panel	Front Panel without Handle	14.9 mm
20846-426	Front Panel	Front Panel without Handle	20 mm
20846-427	Front Panel	Front Panel without Handle	25 mm
20846-428	Front Panel	Front Panel without Handle	30.1 mm
20846-429	Front Panel	Front Panel without Handle	35.2 mm
20846-430	Front Panel	Front Panel without Handle	40.3 mm
20846-431	Front Panel	Front Panel without Handle	50.5 mm
20846-432	Front Panel	Front Panel without Handle	60.6 mm
20846-433	Front Panel	Front Panel without Handle	70.8 mm
20846-434	Front Panel	Front Panel without Handle	106.3 mm
20846-436	Front Panel	Front Panel without Handle	141.9 mm
20846-442	Front Panel	Front Panel without Handle	14.9 mm
20846-443	Front Panel	Front Panel without Handle	20 mm
20846-444	Front Panel	Front Panel without Handle	25 mm
20846-445	Front Panel	Front Panel without Handle	30.1 mm
20846-446	Front Panel	Front Panel without Handle	35.2 mm

Katalognummer	Product Type	Typ	Bredd
20846-447	Front Panel	Front Panel without Handle	40.3 mm
20846-448	Front Panel	Front Panel without Handle	50.5 mm
20846-449	Front Panel	Front Panel without Handle	60.6 mm
20846-450	Front Panel	Front Panel without Handle	70.8 mm
20846-451	Front Panel	Front Panel without Handle	106.3 mm
20846-452	Front Panel	Front Panel without Handle	141.9 mm
20846-456	Front Panel	Front Panel without Handle	80.9 mm

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE