

Interscale 19" Rack Mount Chassis, Perforated

Energiföretag



Flexible 19" Chassis with integrated EMC protection and perforated side. Based on the nVent SCHROFF Interscale platform and developed in accordance with IEC 60297-3-109.

CERTIFIERING



FUNKTIONER

Modular desktop case consisting of 4 assembled parts, with perforated sides

Developed according to IEC 60297-3-109 (under progress at IEC)

Integrated EMC protection

Ingress protection up to IP 20

Color RAL 7016

Modified or customized cases upon request

SPECIFIKATIONER

Table 1/2

Katalognummer	Rack Height	Djup	Package Quantity	Usable Width	Montering	Uppfyller kraven enligt
14826-105	1 U	221 mm	1	444 mm	Rack	IEC 60297-3-100

Katalognummer	Rack Height	Djup	Package Quantity	Usable Width	Montering	Uppfyller kraven enligt
14826-107	1 U	310 mm	1	444 mm	Rack	IEC 60297-3-100
14826-205	2 U	221 mm	1	444 mm	Rack	IEC 60297-3-100
14826-207	2 U	310 mm	1	444 mm	Rack	IEC 60297-3-100
14826-305	3 U	221 mm	1	444 mm	Rack	IEC 60297-3-100
14826-307	3 U	310 mm	1	444 mm	Rack	IEC 60297-3-100

Table 2/2

Katalognummer	EMC Shielding	Product Family	Product Type	Typ
14826-105	Ja	Interscale	Small Form Factor Case	Perforerad
14826-107	Ja	Interscale	Small Form Factor Case	Perforerad
14826-205	Ja	Interscale	Small Form Factor Case	Perforerad
14826-207	Ja	Interscale	Small Form Factor Case	Perforerad
14826-305	Ja	Interscale	Small Form Factor Case	Perforerad
14826-307	Ja	Interscale	Small Form Factor Case	Perforerad

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE