

MultipacPRO 19" Chassis, Aluminum, Plain Top and Base

Power Utilities



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have plain top and bottom cover.

CERTIFIERINGAR



DESIGN

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

SPECIFIKATIONER

Table 1/2

Katalognummer	Rackhöjd	Djup	Användbar bredd	Montering	Överensstämmer med.	EMC-skärmning
20860-601	1 U	220 mm	403 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	Nej (kan eftermonteras)
20860-602	1 U	280 mm	403 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	Nej (kan eftermonteras)
20860-603	1 U	340 mm	4 mm	Rack	IEC 60297-3-100	Nej (kan eftermonteras)
20860-604	2 U	220 mm	4 mm	Rack	IEC 60297-3-100	Nej (kan eftermonteras)
20860-605	2 U	280 mm	403 mm	Rack	IEC 60297-3-100	Nej (kan eftermonteras)
20860-606	2 U	340 mm	403 mm	Rack	IEC 60297-3-100	Nej (kan eftermonteras)
20860-607	3 U	280 mm	403 mm	Rack	IEC 60297-3-100	Nej (kan eftermonteras)
20860-608	3 U	340 mm	403 mm	Rack	IEC 60297-3-100	Nej (kan eftermonteras)
20860-609	3 U	400 mm	403 mm	Rack	IEC 60297-3-100	Nej (kan eftermonteras)
20860-610	3 U	460 mm	4 mm	Rack	IEC 60297-3-100	Nej (kan eftermonteras)
20860-611	4 U	280 mm	4 mm	Rack	IEC 60297-3-100	Nej (kan eftermonteras)
20860-612	4 U	340 mm	403 mm	Rack	IEC 60297-3-100	Nej (kan eftermonteras)
20860-613	4 U	400 mm	403 mm	Rack	IEC 60297-3-100	Nej (kan eftermonteras)
20860-614	4 U	460 mm	403 mm	Rack	IEC 60297-3-100	Nej (kan eftermonteras)
20860-615	5 U	460 mm	403 mm	Rack	IEC 60297-3-100	Nej (kan eftermonteras)

Table 2/2

Katalognummer	Produktfamilj	Produkttyp	Typ	Certifieringar
20860-601	MultipacPRO	Subrack/chassi	Fast sken	RoHS

Katalognummer	Produktfamilj	Produkttyp	Typ	Certifieringar
20860-602	MultipacPRO	Subrack/chassi	Fast sken	RoHS
20860-603	MultipacPRO	Subrack/chassi	Fast sken	
20860-604	MultipacPRO	Subrack/chassi	Fast sken	
20860-605	MultipacPRO	Subrack/chassi	Fast sken	RoHS
20860-606	MultipacPRO	Subrack/chassi	Fast sken	RoHS
20860-607	MultipacPRO	Subrack/chassi	Fast sken	RoHS
20860-608	MultipacPRO	Subrack/chassi	Fast sken	RoHS
20860-609	MultipacPRO	Subrack/chassi	Fast sken	RoHS
20860-610	MultipacPRO	Subrack/chassi	Fast sken	
20860-611	MultipacPRO	Subrack/chassi	Fast sken	
20860-612	MultipacPRO	Subrack/chassi	Fast sken	RoHS
20860-613	MultipacPRO	Subrack/chassi	Fast sken	RoHS
20860-614	MultipacPRO	Subrack/chassi	Fast sken	RoHS
20860-615	MultipacPRO	Subrack/chassi	Fast sken	RoHS

YTTERLIGARE PRODUKTINFORMATION

Please order front handles separately.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE