

# MultipacPRO 19" Chassis, Steel, AlZn, Plain Top and Base

## Energiföretag



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version is produced from sheet metal, Al-Zn coated and have plain top and bottom covers.

## CERTIFIERING



## FUNKTIONER

Steel (AlZn coated) with Al extrusion front panel

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

EMC shielding: Approx. 20dB(A) at 2GHz without shielding material. >40dB(A) at 1Ghz with addition of stainless steel gasket between front panel and case body

Internal and external dimensions in accordance with: IEC 60297-3-101

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

## SPECIFIKATIONER

Table 1/2

| Katalognummer | Rack Height | Djup   | Usable Width | Montering | Uppfyller kraven enligt          | EMC Shielding      |
|---------------|-------------|--------|--------------|-----------|----------------------------------|--------------------|
| 20860-120     | 1 U         | 220 mm | 447 mm       | Rack      | IEC 60297-3-100, IEC 60297-3-105 | No (Retrofittable) |
| 20860-121     | 1 U         | 280 mm | 447 mm       | Rack      | IEC 60297-3-100, IEC 60297-3-105 | No (Retrofittable) |
| 20860-122     | 1 U         | 340 mm | 447 mm       | Rack      | IEC 60297-3-100, IEC 60297-3-105 | No (Retrofittable) |
| 20860-126     | 2 U         | 280 mm | 447 mm       | Rack      | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-127     | 2 U         | 340 mm | 447 mm       | Rack      | IEC 60297-3-100                  | No (Retrofittable) |

Table 2/2

| Katalognummer | Product Family | Product Type    | Typ   |
|---------------|----------------|-----------------|-------|
| 20860-120     | MultipacPRO    | Subrack/Chassis | Solid |
| 20860-121     | MultipacPRO    | Subrack/Chassis | Solid |
| 20860-122     | MultipacPRO    | Subrack/Chassis | Solid |
| 20860-126     | MultipacPRO    | Subrack/Chassis | Solid |
| 20860-127     | MultipacPRO    | Subrack/Chassis | Solid |

## ADDITIONAL PRODUCT DETAILS

Please order front handles separately.

Telescopic slides cannot be used.

Further versions with steel front panel (pizza box) available on request.

Standardised internal mounting kits cannot be used.

## VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på [www.nvent.com](http://www.nvent.com) och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister,

egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**