


Outdoor Unibody HEX

Energiföretag



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity.

CERTIFIERING



FUNKTIONER

Double-walled, Al

Forced heat dissipation via integrated heat exchanger in the door, max. 70 W/K

IP 55

One-piece inner case with removable outer cladding

SPECIFIKATIONER

Table 1/2

Katalognummer	Product Type	Product Family	Rack Height	Höjd	Bredd	Djup
11249-016	Outdoor Cabinet	Unibody	25 U	1330 mm	700 mm	500 mm

Table 2/2

Katalognummer	Wall Type	Door Type	Access	Nedkylning	EMC Shielding	Uppfyller kraven enligt
11249-016	Double Walled	Single Door	Front	Air-to-Air Heat Exchanger	Nej	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE