

PBC flätad strömshunt

Energiföretag



CERTIFIERING



FUNKTIONER

Ideal for transformer-busduct link

Solid palms can be drilled to fit customer specific designs

Extra flexible power connection and good resistance to vibration

SPECIFIKATIONER

Table 1/2

Katalognummer	Artikelnummer	ΔT 30 K	ΔT 50 K	A	B	C
PBC100X250	564000	349 A	462 A	35 mm	40 mm	7 mm

Table 2/2


Katalognummer	Artikelnummer	2 Bar Current Coefficient
---------------	---------------	---------------------------

PBC100X250	564000	1.72
------------	--------	------

ADDITIONAL PRODUCT DETAILS

When used in parallel, the two shunts must be spaced with a minimum distance equal to the thickness of the shunt to allow air cooling.

DIAGRAM



VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE