

RackPower Basic PDU, RB0xxx, 230/400 VAC, 3-phase

Energiföretag

Modular, compact PDU. Using a 1 U aluminum chassis the PDU can easily be integrated in a rack with C13 / C19 Combo outlets.

FUNKTIONER

RackPower Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage Range 200-240/346-415VAC, 3-phase WYE

Connecting cable 6", with IEC 60309 3P+N+E connector

C13 and C13/C19 Combo outlets

1RU aluminum profile

Adjustable Toolless Mounting

SPECIFIKATIONER

Table 1/2

Katalognummer	Product Type	Socket Type	Färg	Längd	Växelström	Djup
RB0450	Socket Strip	IEC C13, IEC C13/C19	Svart	1490 mm	230 V	55 mm
RB0850	Socket Strip	IEC C13, IEC C13/C19	Svart	1780 mm	230 V	55 mm

Table 2/2

Katalognummer	Bredd
RB0450	56 mm
RB0850	56 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE