

# RackPower PDU, RP1xxx, 230/400 VAC, 3-phase

## Energiföretag

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design with only 44 mm height.

### FUNKTIONER

RackPower RP1xxx Intelligent Power Distribution Units monitors input power of the entire PDU, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 200-240/346-415VAC, 3-phase WYE

Connecting cable 6" with IEC 60309 3P+N+E connector

C13 and C13/C19 Combo outlets

### SPECIFIKATIONER

Table 1/2

Katalognummer	Product Type	Socket Type	Färg	Längd	Växelström	Funktion
RP1450	Socket Strip	IEC C13, IEC C13/C19	Svart	1490 mm	230 V	Input Monitored
RP1850	Socket Strip	IEC C13, IEC C13/C19	Svart	1780 mm	230 V	Input Monitored
RP1950	Socket Strip	IEC C13, IEC C13/C19	Svart	1826 mm	230 V	Input Monitored

Table 2/2

Katalognummer	Djup	Bredd
RP1450	55 mm	56 mm
RP1850	55 mm	56 mm
RP1950	75 mm	56 mm

## ADDITIONAL PRODUCT DETAILS

---

Please order bracket for vertical mounting separately.

## VARNING

---

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på [www.nvent.com](http://www.nvent.com) och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**