

RatiopacPRO 19" Rack Mount Case, Retrofittable Shielding With Handles

Energiföretag



The nVent SCHROFF RatiopacPRO case provides electronics protection for 19" and individual electronic assemblies. This flexible and robust case is simple to convert from desktop to a 19" rack mount case and includes four different style options. This version of the case provides mounting brackets and handles for assembly into a 19" rack.

CERTIFIERING



FUNKTIONER

Cases for individual assembly with 19" standard components or specific internal mounting, e.g. with mounting plate

Designed for insertion/extractor handles in accordance with IEC 60297-3-102 and IEEE 1101.10 for CompactPCI and VME64x applications

Version with 19" mounting brackets with front handles

Retrofittable EMC shielding

For board depth 160 mm, 220 mm, 280 mm, and 340 mm (depending on case depth)

No visible screws; cladding parts removable without tools

Symmetrical design, identical front and rear side

Conforms with DIN EN 62368-1

SPECIFIKATIONER

Table 1/3

Katalognummer	Rack Height	Djup	Package Quantity	Usable Height	Usable Width	Front Frame Construction
24572-620	2 U	255.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-623	2 U	315.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-624	2 U	375.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-625	2 U	435.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-626	2 U	495.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-630	3 U	255.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-633	3 U	315.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-634	3 U	375.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-635	3 U	435.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-636	3 U	495.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-640	4 U	255.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails

Katalognummer	Rack Height	Djup	Package Quantity	Usable Height	Usable Width	Front Frame Construction
24572-643	4 U	315.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-644	4 U	375.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-645	4 U	435.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-646	4 U	495.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-660	6 U	255.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-663	6 U	315.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-664	6 U	375.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-665	6 U	435.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-666	6 U	495.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails

Table 2/3

Katalognummer	Cooling Option	Uppfyller kraven enligt	EMC Shielding	Höjd	Product Family	Product Type
---------------	----------------	-------------------------	---------------	------	----------------	--------------

24572-620	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Case
24572-623	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Case
24572-624	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Case
24572-625	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Case
24572-626	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Case
24572-630	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Case
24572-633	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Case
24572-634	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Case

24572-635	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Case
24572-636	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Case
24572-640	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Case
24572-643	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Case
24572-644	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Case
24572-645	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Case
24572-646	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Case
24572-660	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Case

24572-663	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Case
24572-664	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Case
24572-665	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Case
24572-666	Nej	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Case

Table 3/3

Katalognummer	Protection Rating	Rack Width	Statisk belastning	Typ	Bredd
24572-620	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-623	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-624	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-625	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-626	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-630	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm

Katalognummer	Protection Rating	Rack Width	Statisk belastning	Typ	Bredd
24572-633	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-634	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-635	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-636	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-640	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-643	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-644	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-645	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-646	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-660	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-663	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-664	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-665	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-666	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm

ADDITIONAL PRODUCT DETAILS

Modifications (special colours or sizes).

Custom solutions (cut-outs in top cover, base plate or side panels).

Assembly service from 1 piece.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE