

Varistar CP 19" Swing Frame Trim

Energiföretag

Varistar CP swing frame provides optimum space usage inside the rack. The swing frames come with handles.

FUNKTIONER

Includes handle and cut-out for cable eyes

To cover the gap between swing frame and cabinet upright for 800 mm wide cabinets

Maximum swing bracket: 120 or 160

For swing frame with load-carrying capacity 150 kg, a stop is recommended for security reasons

Locking no. 333

Spare key for DIN semi-profile cylinder

SPECIFIKATIONER

Table 1/2

Katalognummer	Rack Height	Färg	Color Code	Material	Product Type	Protection Rating
21630-746	24 U	Black Grey	RAL 7021	Stål	Cabinet/Rack Frame	IP20
21630-749	24 U	Black Grey	RAL 7021	Stål	Cabinet/Rack Frame	IP20
21630-747	33 U	Black Grey	RAL 7021	Stål	Cabinet/Rack Frame	IP20
21630-750	33 U	Black Grey	RAL 7021	Stål	Cabinet/Rack Frame	IP20
21630-748	42 U	Black Grey	RAL 7021	Stål	Cabinet/Rack Frame	IP20
21630-751	42 U	Black Grey	RAL 7021	Stål	Cabinet/Rack Frame	IP20

Table 2/2

Katalognummer	Typ	Fungerar med
---------------	-----	--------------

21630-746	Swing	Varistar, Varistar CP
21630-749	Swing	Varistar, Varistar CP
21630-747	Swing	Varistar, Varistar CP
21630-750	Swing	Varistar, Varistar CP
21630-748	Swing	Varistar, Varistar CP
21630-751	Swing	Varistar, Varistar CP

ADDITIONAL PRODUCT DETAILS

Varistar CP swing frame provides optimum space usage inside the rack. The swing frames come with handles.

Please purchase the grounding kit separately.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE