

# Varistar CP Base Plate, One-Piece

## Energiföretag

The base plate is solid and covers the base of the cabinet.

### FUNKTIONER

The base plate is solid and covers the base of the cabinet

Is assembled from outside

### SPECIFIKATIONER

Table 1/2

| Katalognummer | Bredd  | Djup    | Protection Rating | Färg       | Color Code | Uppfyller kraven enligt |
|---------------|--------|---------|-------------------|------------|------------|-------------------------|
| 21630-320     | 600 mm | 300 mm  |                   | Black Grey | RAL 7021   |                         |
| 21630-628     | 600 mm | 300 mm  |                   | Black Grey | RAL 7021   |                         |
| 21630-322     | 600 mm | 600 mm  |                   | Black Grey | RAL 7021   |                         |
| 21630-323     | 600 mm | 800 mm  |                   | Black Grey | RAL 7021   |                         |
| 21630-324     | 600 mm | 900 mm  |                   | Black Grey | RAL 7021   |                         |
| 21630-325     | 600 mm | 1000 mm |                   | Black Grey | RAL 7021   |                         |
| 21630-326     | 600 mm | 1100 mm |                   | Black Grey | RAL 7021   |                         |
| 21630-327     | 600 mm | 1200 mm |                   | Black Grey | RAL 7021   |                         |
| 21630-629     | 600 mm | 600 mm  |                   | Black Grey | RAL 7021   |                         |

| Katalognummer | Bredd  | Djup    | Protection Rating | Färg       | Color Code | Uppfyller kraven enligt     |
|---------------|--------|---------|-------------------|------------|------------|-----------------------------|
| 21630-630     | 600 mm | 800 mm  |                   | Black Grey | RAL 7021   |                             |
| 21630-631     | 600 mm | 900 mm  |                   | Black Grey | RAL 7021   |                             |
| 21630-632     | 600 mm | 1000 mm |                   | Black Grey | RAL 7021   |                             |
| 21630-633     | 600 mm | 1100 mm |                   | Black Grey | RAL 7021   |                             |
| 21630-634     | 600 mm | 1200 mm |                   | Black Grey | RAL 7021   |                             |
| 21630-826     | 600 mm | 600 mm  | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-827     | 600 mm | 800 mm  | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-828     | 600 mm | 900 mm  | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-829     | 600 mm | 1000 mm | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-830     | 600 mm | 1100 mm | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-831     | 600 mm | 1200 mm | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-330     | 800 mm | 600 mm  |                   | Black Grey | RAL 7021   |                             |
| 21630-635     | 800 mm | 600 mm  |                   | Black Grey | RAL 7021   |                             |
| 21630-832     | 800 mm | 600 mm  | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-331     | 800 mm | 800 mm  |                   | Black Grey | RAL 7021   |                             |
| 21630-332     | 800 mm | 900 mm  |                   | Black Grey | RAL 7021   |                             |
| 21630-333     | 800 mm | 1000 mm |                   | Black Grey | RAL 7021   |                             |
| 21630-334     | 800 mm | 1100 mm |                   | Black Grey | RAL 7021   |                             |

| Katalognummer | Bredd  | Djup    | Protection Rating | Färg       | Color Code | Uppfyller kraven enligt     |
|---------------|--------|---------|-------------------|------------|------------|-----------------------------|
| 21630-335     | 800 mm | 1200 mm |                   | Black Grey | RAL 7021   |                             |
| 21630-636     | 800 mm | 800 mm  |                   | Black Grey | RAL 7021   |                             |
| 21630-637     | 800 mm | 900 mm  |                   | Black Grey | RAL 7021   |                             |
| 21630-638     | 800 mm | 1000 mm |                   | Black Grey | RAL 7021   |                             |
| 21630-639     | 800 mm | 1100 mm |                   | Black Grey | RAL 7021   |                             |
| 21630-640     | 800 mm | 1200 mm |                   | Black Grey | RAL 7021   |                             |
| 21630-833     | 800 mm | 800 mm  | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-834     | 800 mm | 900 mm  | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-835     | 800 mm | 1000 mm |                   | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-836     | 800 mm | 1100 mm | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |
| 21630-837     | 800 mm | 1200 mm | IP20              | Black Grey | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 |

Table 2/2

| Katalognummer | Material | Product Type      | Fungerar med |
|---------------|----------|-------------------|--------------|
| 21630-320     | Stål     | Cabinet/Rack Base |              |
| 21630-628     | Stål     | Cabinet/Rack Base |              |
| 21630-322     | Stål     | Cabinet/Rack Base |              |
| 21630-323     | Stål     | Cabinet/Rack Base |              |
| 21630-324     | Stål     | Cabinet/Rack Base |              |
| 21630-325     | Stål     | Cabinet/Rack Base |              |

| Katalognummer | Material | Product Type      | Fungerar med |
|---------------|----------|-------------------|--------------|
| 21630-326     | Stål     | Cabinet/Rack Base |              |
| 21630-327     | Stål     | Cabinet/Rack Base |              |
| 21630-629     | Stål     | Cabinet/Rack Base |              |
| 21630-630     | Stål     | Cabinet/Rack Base |              |
| 21630-631     | Stål     | Cabinet/Rack Base |              |
| 21630-632     | Stål     | Cabinet/Rack Base |              |
| 21630-633     | Stål     | Cabinet/Rack Base |              |
| 21630-634     | Stål     | Cabinet/Rack Base |              |
| 21630-826     | Stål     | Cabinet/Rack Base | Varistar CP  |
| 21630-827     | Stål     | Cabinet/Rack Base | Varistar CP  |
| 21630-828     | Stål     | Cabinet/Rack Base | Varistar CP  |
| 21630-829     | Stål     | Cabinet/Rack Base | Varistar CP  |
| 21630-830     | Stål     | Cabinet/Rack Base | Varistar CP  |
| 21630-831     | Stål     | Cabinet/Rack Base | Varistar CP  |
| 21630-330     | Stål     | Cabinet/Rack Base |              |
| 21630-635     | Stål     | Cabinet/Rack Base |              |
| 21630-832     | Stål     | Cabinet/Rack Base | Varistar CP  |
| 21630-331     | Stål     | Cabinet/Rack Base |              |

| Katalognummer | Material | Product Type      | Fungerar med |
|---------------|----------|-------------------|--------------|
| 21630-332     | Stål     | Cabinet/Rack Base |              |
| 21630-333     | Stål     | Cabinet/Rack Base |              |
| 21630-334     | Stål     | Cabinet/Rack Base |              |
| 21630-335     | Stål     | Cabinet/Rack Base |              |
| 21630-636     | Stål     | Cabinet/Rack Base |              |
| 21630-637     | Stål     | Cabinet/Rack Base |              |
| 21630-638     | Stål     | Cabinet/Rack Base |              |
| 21630-639     | Stål     | Cabinet/Rack Base |              |
| 21630-640     | Stål     | Cabinet/Rack Base |              |
| 21630-833     | Stål     | Cabinet/Rack Base | Varistar CP  |
| 21630-834     | Stål     | Cabinet/Rack Base | Varistar CP  |
| 21630-835     | Stål     | Cabinet/Rack Base | Varistar CP  |
| 21630-836     | Stål     | Cabinet/Rack Base | Varistar CP  |
| 21630-837     | Stål     | Cabinet/Rack Base | Varistar CP  |

## ADDITIONAL PRODUCT DETAILS

This base plate is used for applications which don't require cable entry from the base.

Please purchase the grounding kit separately.

## WARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på [www.nvent.com](http://www.nvent.com) och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister,

egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**