

Varistar CP Bottom Rear Panel, Shortened

Energiföretag

Shortened Rear Panel available for IP20, IP55 and EMC applications.

Shortened rear panels ensure efficient cable management.

FUNKTIONER

Screw fixed, Robust and Single person mountable Side Panel

Plain or with brush strip

Height of connection plate 400 mm

SPECIFIKATIONER

Table 1/2

Katalognummer	Rack Height	Höjd	Bredd	Protection Rating	Färg	Color Code
21630-354	38 U	1800 mm	600 mm	IP55	Black Grey	RAL 7021
21630-355	38 U	1800 mm	800 mm	IP55	Black Grey	RAL 7021
21630-356	42 U	2000 mm	600 mm	IP55	Black Grey	RAL 7021
21630-357	42 U	2000 mm	800 mm	IP55	Black Grey	RAL 7021
21630-358	47 U	2200 mm	600 mm	IP55	Black Grey	RAL 7021
21630-359	47 U	2200 mm	800 mm	IP55	Black Grey	RAL 7021

Table 2/2

Katalognummer	Product Type
21630-354	Cabinet Door

Katalognummer	Product Type
21630-355	Cabinet Door
21630-356	Cabinet Door
21630-357	Cabinet Door
21630-358	Cabinet Door
21630-359	Cabinet Door

ADDITIONAL PRODUCT DETAILS

The height of the rear panel is 400 mm less than the cabinet height to accomodate the connecting plate.

Please purchase the grounding kit separately.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE