

Varistar CP Cabinet Frame, Seismic Heavy Load

Energiföretag

Welded, steel enclosure engineered specifically to protect equipment in areas with seismic activity and satisfy Bellcore Zore 4 requirements.

FUNKTIONER

St, 1.5 mm, zinc-plated, finish: powder-coated

Earthquake resistance to Bellcore Zone 4

Welded heavy-duty frame with strengthening brackets, RAL 7021

Dynamic load-carrying capacity 500 kg to IEC 61587-2

SPECIFIKATIONER

Table 1/3

Katalognummer	Rack Height	Höjd	Bredd	Djup	Shock and Vibration Tolerance	Färg
20630-269	42 U	2000 mm	600 mm	1000 mm	5 g (force)	Black Grey
20630-270	42 U	2000 mm	600 mm	1200 mm	5 g (force)	Black Grey
20630-271	42 U	2000 mm	800 mm	1000 mm	5 g (force)	Black Grey
20630-272	42 U	2000 mm	800 mm	1200 mm	5 g (force)	Black Grey
20630-273	33 U	1600 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-274	33 U	1600 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-275	33 U	1600 mm	800 mm	600 mm	5 g (force)	Black Grey

Katalognummer	Rack Height	Höjd	Bredd	Djup	Shock and Vibration Tolerance	Färg
20630-276	33 U	1600 mm	800 mm	800 mm	5 g (force)	Black Grey
20630-277	38 U	1800 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-278	38 U	1800 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-279	38 U	1800 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-280	38 U	1800 mm	800 mm	800 mm	5 g (force)	Black Grey
20630-281	42 U	2000 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-282	42 U	2000 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-283	42 U	2000 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-284	42 U	2000 mm	800 mm	1600 mm	5 g (force)	Black Grey
20630-285	42 U	2200 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-286	47 U	2200 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-287	47 U	2200 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-288	47 U	2200 mm	800 mm	800 mm	5 g (force)	Black Grey

Table 2/3

Katalognummer	Color Code	Uppfyller kraven enligt	Frame Material	Material	Product Type	Statisk belastning
20630-269	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-270	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-271	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf

Katalognummer	Color Code	Uppfyller kraven enligt	Frame Material	Material	Product Type	Statisk belastning
20630-272	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-273	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-274	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-275	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-276	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-277	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-278	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-279	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-280	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-281	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-282	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-283	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-284	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-285	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-286	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-287	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-288	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf

Table 3/3

Katalognummer	Typ	Fungerar med
---------------	-----	--------------

20630-269	Heavy Load	Varistar CP
20630-270	Heavy Load	
20630-271	Heavy Load	Varistar CP
20630-272	Heavy Load	Varistar CP
20630-273	Heavy Load	Varistar CP
20630-274	Heavy Load	Varistar CP
20630-275	Heavy Load	Varistar CP
20630-276	Heavy Load	Varistar CP
20630-277	Heavy Load	Varistar CP
20630-278	Heavy Load	Varistar CP
20630-279	Heavy Load	Varistar CP
20630-280	Heavy Load	Varistar CP
20630-281	Heavy Load	Varistar CP
20630-282	Heavy Load	Varistar CP
20630-283	Heavy Load	Varistar CP
20630-284	Heavy Load	Varistar CP
20630-285	Heavy Load	Varistar CP
20630-286	Heavy Load	Varistar CP
20630-287	Heavy Load	Varistar CP

20630-288	Heavy Load	Varistar CP
-----------	------------	-------------

ADDITIONAL PRODUCT DETAILS

Please order attachments and components separately.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE