

Varistar CP Double Steel Door, Perforated With 3-Point Electronic Locking

Energiföretag

Perforated Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

FUNKTIONER

Double perforated steel door with 3-point locking for IP 20 protection class

Lever handle with push button, key

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with DIN profile half cylinder

SPECIFIKATIONER

Table 1/3

Katalognummer	Rack Height	Höjd	Bredd	Färg	Color Code	Uppfyller kraven enligt
21630-820	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-821	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-822	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-823	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-824	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-825	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1

Table 2/3

Katalognummer	Ytbeläggning	Locking Type	Material	Product Type	Protection Rating	Typ
21630-820	Pulverlackerad	3-Point Locking, Electronic	Stål	Cabinet Door	IP20	Steel Double Door, Perforated
21630-821	Pulverlackerad	3-Point Locking, Electronic	Stål	Cabinet Door	IP20	Steel Double Door, Perforated
21630-822	Pulverlackerad	3-Point Locking, Electronic	Stål	Cabinet Door	IP20	Steel Double Door, Perforated
21630-823	Pulverlackerad	3-Point Locking, Electronic	Stål	Cabinet Door	IP20	Steel Double Door, Perforated
21630-824	Pulverlackerad	3-Point Locking, Electronic	Stål	Cabinet Door	IP20	Steel Double Door, Perforated
21630-825	Pulverlackerad	3-Point Locking, Electronic	Stål	Cabinet Door	IP20	Steel Double Door, Perforated

Table 3/3

Katalognummer	Fungerar med
21630-820	Varistar CP
21630-821	Varistar CP
21630-822	Varistar CP
21630-823	Varistar CP
21630-824	Varistar CP
21630-825	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE