

Varistar CP Seismic Heavy Load Cabinet, Bellcore Zone 4, EMC

Energiföretag

Cabinet with IP 55 and EMC compliance for extreme seismic environments tested to Bellcore zone 4 with a dynamic load-carrying capacity of 500 kg. Customised solutions with higher loading are available. The cabinet is widely used in ICT applications in earthquake prone areas, Construction and Shipping Facilities, Airports, Railways and many more.

Other dimensions and versions can be configured on the Online Configurator

FUNKTIONER

Earthquake secure up to Bellcore Zone 4, tested with 500 KGs per Telcordia GR-63 Core, NEBS Certified

Static load-carrying capacity 1600 kg

Type of Protection IP55

High Shielding capability tested per IEC 61587-3, with EN45545-2 Fire safety gasket

SPECIFIKATIONER

Table 1/3

Katalognummer	Frame Material	Rack Height	Höjd	Bredd	Djup	Statisk belastning
10630-048	Stål	42 U	2000 mm	600 mm	800 mm	1600 kgf

Table 2/3

Katalognummer	Protection Rating	Uppfyller kraven enligt	Färg	Color Code	Material	Shock and Vibration Tolerance

10630-048	IP55	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-3, IEC 61587-1, IEC 61587-2, EN 45545-2	Black Grey	RAL 7021	Stål	5 g (force)
-----------	------	--	------------	----------	------	-------------

Table 3/3

Katalognummer	Fungerar med
10630-048	Varistar CP

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE