

Varistar CP Steel Door, Perforated With Multi-Point Locking

Energiföretag

EMC doors with good contact with the frame and gasket to achieve high attenuation.

The 4 point locking helps achieve necessary contact to avoid EMI effects on electronics.

FUNKTIONER

Perforated door with 4-point locking for EMC applications

Interior galvanized

Opening angle 180°

Lever handle with push button

SPECIFIKATIONER

Table 1/2

Katalognummer	Rack Height	Höjd	Bredd	Färg	Color Code	Locking Type
21630-533	24 U	1200 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-534	24 U	1200 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-535	29 U	1400 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-536	29 U	1400 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-537	33 U	1600 mm	600 mm	Black Grey	RAL 7021	4-Point Locking
21630-538	33 U	1600 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-539	38 U	1800 mm	600 mm	Black Grey	RAL 7021	4-Point Locking

Katalognummer	Rack Height	Höjd	Bredd	Färg	Color Code	Locking Type
21630-540	38 U	1800 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-541	42 U	2000 mm	600 mm	Black Grey	RAL 7021	4-Point Locking
21630-542	42 U	2000 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-543	47 U	2200 mm	600 mm	Black Grey	RAL 7021	5-Point Locking
21630-544	47 U	2200 mm	800 mm	Black Grey	RAL 7021	5-Point Locking

Table 2/2

Katalognummer	Material	Product Type	Typ
21630-533	Stål	Cabinet Door	Steel Door, Perforated
21630-534	Stål	Cabinet Door	Steel Door, Perforated
21630-535	Stål	Cabinet Door	Steel Door, Perforated
21630-536	Stål	Cabinet Door	Steel Door, Perforated
21630-537	Stål	Cabinet Door	Steel Door, Perforated
21630-538	Stål	Cabinet Door	Steel Door, Perforated
21630-539	Stål	Cabinet Door	Steel Door, Perforated
21630-540	Stål	Cabinet Door	Steel Door, Perforated
21630-541	Stål	Cabinet Door	Steel Door, Perforated
21630-542	Stål	Cabinet Door	Steel Door, Perforated
21630-543	Stål	Cabinet Door	Steel Door, Perforated
21630-544	Stål	Cabinet Door	Steel Door, Perforated

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE