

Varistar CP Steel Door, Plain With 3-Point Locking, IP55

Energiföretag

Steel door with mounting frame on inside, 3 point locking and with Lever handle with built-in push button.

FUNKTIONER

Steel door with three point locking for IP 55 protection class

Lever handle with built-in push button

Opening angle 180°

SPECIFIKATIONER

Table 1/3

Katalognummer	Rack Height	Höjd	Bredd	Färg	Color Code	Uppfyller kraven enligt
21630-171	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-210	24 U	1200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-211	29 U	1400 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-212	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-213	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-214	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-215	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-216	24 U	1200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1

Katalognummer	Rack Height	Höjd	Bredd	Färg	Color Code	Uppfyller kraven enligt
21630-217	29 U	1400 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-218	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-219	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-220	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1

Table 2/3						
Katalognummer	Ytbeläggning	Locking Type	Material	Product Type	Protection Rating	Typ
21630-171	Pulverlackerad	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-210	Pulverlackerad	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-211	Pulverlackerad	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-212	Pulverlackerad	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-213	Pulverlackerad	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-214	Pulverlackerad	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-215	Pulverlackerad	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-216	Pulverlackerad	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-217	Pulverlackerad	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-218	Pulverlackerad	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-219	Pulverlackerad	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-220	Pulverlackerad	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door

Table 3/3

Katalognummer	Fungerar med
21630-171	Varistar CP
21630-210	Varistar CP
21630-211	Varistar CP
21630-212	Varistar CP
21630-213	Varistar CP
21630-214	Varistar CP
21630-215	Varistar CP
21630-216	Varistar CP
21630-217	Varistar CP
21630-218	Varistar CP
21630-219	Varistar CP
21630-220	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE