

Connection Kit for PI Heaters Into Junction Box

nVent RAYCHEM C20-PI-M0 and C20-PI-PA are a range of kits to connect polymer insulated (PI) heaters into a junction box. The C20-PI-M0-KIT contains cable gland Ex e (M20), nickel-plated brass, for use with XPI cold leads up to -55 °C. The C20-PI-PA-KIT contains cable gland Ex e (M20), polyamide, for use with XPI cold leads up to -40 °C. All kits include green/yellow sleeves for braid and locknut.

DESIGN

Hazardous area approved

Simple and fast to install, easy to maintain

Reliable during long life: 10 year product warranty available

SPECIFIKATIONER

Gängtyp: Metrisk

Table 1/1

Katalognummer	Artikelnamn	Material	Slutför	Omgivningstemperatur	Lämplig för PI-kablar med diameterområde
1244-019669	C20-PI-PA-KIT	Polyamid	Obehandlad	-40 to 75 °C	4 – 13 mm
1244-019670	C20-PI-M0-KIT	Mässing	Nickel-Plated	-55 to 90 °C	5 – 14 mm

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Vårt starka utbud av varumärken:

RAYCHEM PYROTENAX TRACER NUHEAT