

NGC-40 Series, Power Termination Module



nVent RAYCHEM NGC-40 Series - Power Termination Module accepts a primary and redundant power supply input, also accepts CAN bus inputs and provides for termination of the CAN bus. Each NGC-40-PTM can provide power for a maximum of 10 NGC-40 modules.

DESIGN

Din-rail mounted and part of the NGC-40 system

Provides primary power and CAN bus inputs/termination to the NGC-40 system

Easy to install and reliable

SPECIFIKATIONER

Table 1/2

Katalognummer	Artikelnamn	Märkspänning	Spänningstyp	Strömstyrka vid 24 V DC	Drifttemperatur	Höjd
10730-005	NGC-40-PTM	24 V	DC	1.5 A	-40 to 65 °C	87 mm

Table 2/2

Katalognummer	Artikelnamn	Bredd	Djup
10730-005	NGC-40-PTM	45 mm	106.4 mm

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplikering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Vårt starka utbud av varumärken:

RAYCHEM PYROTENAX TRACER NUHEAT