

CompacPRO Rear Panel With Vented Slots



The rear panel with vented slots can be used for the CompacPRO case. The rear panel is bolted on the rear frame.

CERTIFIERINGAR



DESIGN

Al material 3.0 mm

SPECIFIKATIONER

Material:	Aluminium
Yta:	Anodiserad
Fungerar med:	Lådor
Produktfamilj:	CompacPRO
Typ:	Bakre panel
Produkttyp:	Sidopanel

Table 1/1

Katalognummer	Rackhöjd	Rackbredd	Antal i förpackningen	Snabbleverans
30823-027	3U	63HP	1	Nej
30823-033	4U	42HP	1	Nej

Katalognummer	Rackhöjd	Rackbredd	Antal i förpackningen	Snabbleverans
30823-036	4U	63HP	1	Nej
30823-021	3U	28HP	1	Nej
30823-024	3U	42HP	1	Nej
30823-518	4U	84HP	1	Nej
30823-512	2U	84HP	1	Nej
30823-045	6U	63HP	1	Nej
30823-015	2U	42HP	1	Nej
30823-521	6U	84HP	1	Nej
30823-515	3U	84HP	1	Nej

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE